

- Complies with BS EN 7895.
- T2 = heat resistance rating (210°C).
- Automatically disconnect power at the contacts when the lamp is removed.
- 50.8mm fixing centres for non-access versions. Use with mounting blocks MB326E/MT.
- Solid brass plungers and copper plated steel springs maintain plunger pressure throughout their long life.
- Body angle of angled battens set at 30°.
- Access lampholders have integral RL624 ceiling rose base and heat resisting PVC tails.
- All pendants incorporate automatic cord grips and sleeve caps for ease of flexible cord stripping.

Bayonet Cap Cord Grip Lampholders



SEL212

Description	Pack qty.	Cat ref.
Safety Cord Grip Lampholders - Short Skirt	20	SEL212
Safety Cord Grip Lampholders - Home Office Shield	20	SEL214

Straight BC Batten Lampholder



SEL354

Description	Pack qty.	Cat ref.
Three Terminal - Home Office Shield	20	SEL354

Access BC Batten Lampholder



SEL96T

Description	Pack qty.	Cat ref.
Straight 2 Terminal Body, 3 Terminal and Earth Base - Home Office Shield	10	SEL96T
Angled 2 Terminal Body, 3 Terminal and Earth Base - Home Office Shield	10	SEL106T

- Pendant set complies with BS EN 60598-1.
- Capacity of each terminal: 3 x 1.00mm² conductor
- Common base with 'access' batten lampholders.
- Barriers between terminals.
- Flexible pendant cord restraining hooks.
- Fixing centres 50.8mm.
- Feet on base to aid mounting on uneven surfaces.
- 3 separate knockouts accept 1, 2 or 3 x 1.5mm² conductors.
- Optional halo RL602 (see page 36).

Pendant Sets with Access Ceiling Rose



624SEL212/6

Description	Pack qty.	Cat ref.
Safety Pendant Set 6" - Short Skirt	10	624SEL212/6
Safety Pendant Set 9" - Short Skirt	10	624SEL212/9
Safety Pendant Set 12" - Short Skirt	10	624SEL212/12
Safety Shield Pendant Set 6" - Home Office Shield	10	624SEL214/6
Safety Shield Pendant Set 9" - Home Office Shield	10	624SEL214/9
Safety Shield Pendant Set 12" - Home Office Shield	10	624SEL214/12

Super Access Terminal Bank Type Ceiling Rose

Description	Dimensions dia x h (mm)	Pack qty.	Cat ref.
3 Terminals	81 diameter x 26 (halo = 108mm diameter)	10	RL624

Low Energy Pendant



LE212/6

Description	Pack qty.	Cat ref.
Low Energy Pendant	1	LE212/6

- Capacity of earth terminal for mounting blocks:
3 x 1.5mm² cables
- Cable knockout entries:
MB326E/MT - centrally in base. 4 on periphery will accept 16mm x 16mm or 16mm x 25mm mini trunking.

Mounting Blocks

Description	Dimensions dia x h (mm)	Pack qty.	Cat ref.
Round Mounting Box with Earth Terminal	81 x 19	20	MB326E/MT
Round Surface Box 30mm Deep	84 x 30	10	MB2



MB326E/MT