



① It's hassle-free

Providing Temporary Power in a permanent position is no longer dependent on the manufacturer's pole that you have in the van.

Our new B&R MD022105 Metering Enclosure has been designed to meet the requirements of AS/NZS3012, the Victorian SIR's and it fits all proprietary builders poles. We have engineered a product solution that is hassle free because it's ready to install straight out of the box, with

- 1) Tool removable door, for compliance with AS/NZS3012
- 2) 3 neutral links for multiple RCD applications.
- 3) Door padlocking Kit fitted
- 4) New combined service Fuse Locking kit (lock not included) & Tie Bar that does not impede access to din equipment.
- 5) Insulated cable entry for up to 8 flexible cords through bottom of enclosure, with quick engage/release feature. Reversible through 180° to close off opening when not required.



- 6) Universal mounting brackets & fixings to fit all proprietary building poles. The brackets are easily removed when surface mounting the enclosure.

For more information on our comprehensive range of B&R metering enclosure solutions please contact your local hager B&R representative.



Product Overview

MD022105

enclosure for use as temporary building supply in a permanent position. Meets the requirements of AS/NZS3012, VIC SIR's and workcover. Complete with hinged moulded panel space for max 2 meter positions fitted with 100Amp fuse & link plus 21 poles of DIN rail insulated power lead entry and insulated tie bar panel: 400w x 380h, enclosure: 485w x 685h x 275d depth behind panel: 75

For the Electrical Contractor



Metering Enclosures

www.hagerbr.com.au

