



Tehalit

Cable management inside&out

TEHALIT



At a glance

Profiles

Three popular profiles available – chamfered / chamfered, chamfered / round and round / round.

Materials

Available in two materials, uPVC and aluminium, C60 is the ideal choice for all, three-compartment trunking requirements.

Complete

One reference provides base and lid together for ease of ordering (C60 only). Available in 2m and 3m lengths, creating less waste.

Space

170mm x 60mm deep profile creates more space for cabling. Easy fit "Clip-Lok" outlet boxes are 35mm deep.

Knockouts push out

Push-out 'knockouts' between compartments with no need for drilling are smooth, elongated slots, minimising damage to cables and maximising data integrity by respecting bend radii.

Alignment

Compartment knockouts fit into base to aid alignment when fixing the pre-punched trunking base.

Corners

Internal and external adjustable moulded corners for a perfect fit even where the corner is not truly 90 degrees.



Two materials,
one great design

Features

Suitable for both new building projects and refurbishments, the C60 and CA60 ranges offer quality products with good aesthetics, combined with features to make installation and ordering simplicity itself.



Easy to order

- Simple part references
- Base and lid supplied complete
- Available in 2 metre and 3 metre lengths as standard

Easy to install

- Bases are pre-punched – no need to drill through to fix to the wall
- Push-out knockouts between compartments – no need to drill through
- Compartment knockouts fit into base to aid alignment
- Adjustable moulded corners for a perfect fit, even when corner is not truly 90°

Easy to cable

- 170mm x 60mm deep profile allows more space for cabling
- Smooth elongated knockouts between compartments minimise

Potential damage to cables

- Data cable bend radii respected, maximising data integrity
- Outer compartment cable retainers supplied as standard with trunking (2 per metre)

Easy on the eye

- Three popular profiles
- C60 standard in clean, bright white (RAL9010), CA60 available in aluminium, white and grey
- Additional protective film on covers protects surfaces prior to handover

Less time, Less mess, Less hassle

Benefits

Designed with ease of installation in mind, the unique push-out knockouts minimise damage to cables and aid alignment of the base.

With simple references, 3 different profiles to choose from – chamfered / chamfered, chamfered / round and round / round, plus base and lid supplied complete, there has never been an easier way to order.

All bases are pre-punched for fast installation and cable-retaining clips ensure that cables are secure when the covers are removed during installation or maintenance.

The specially designed push-out 'knockouts' between compartments are specifically designed to ensure that the remaining smooth, elongated slots minimise damage to cables but maximise data integrity for data cables by respecting the minimum recommended bend radii. As push-outs, there is also no need to drill holes to feed cables between compartments. The push-outs having been removed, are then used to aid alignment when securing the trunking bases together to the wall.

Internal and external adjustable moulded corners for a perfect fit even where the corner is not truly 90 degrees.



Our “Clip-Lok” outlet boxes simply clip into place and are secured with two internal fixings points which make the box suitable for horizontal or vertical runs. The 35mm deep boxes have sufficient space for today’s modern data requirements.

Contractors installing cable management systems will now find it easier to negotiate corners that are not a perfect ninety degrees, with the introduction of a ‘flexible’ corner for the C60 range.

The corner has a flexible section that slides within itself to the required angle for a perfect fit. Versions are available for both internal and external corners, making it easier to negotiate awkward areas such as pillars.

Installation is easy. The corner section simply clips onto the base section like a normal lid and adjusts automatically to the angle of the base. The corner piece provides an overlap for the joining lid thus ensuring a good finish.



Less time, Less mess, Less hassle

Quality perimeter trunking



Perfect for both new build projects and refurbishment and offering a quality range of products with features to make installation and ordering simplicity itself.



- Base and lids with three profiles to choose from (available complete or separate).
- Corner cover kits (internal and external) plus joint covers.
- Clips, joint covers, infills, retainers, end caps and cable dividers.
- Easy fit outlet boxes.
- Base and lid earthing terminal kits (CA60)

Tehalit, the versatile cable management system from Hager. A name you can trust.

Hager Ltd.
Hortonwood 50
Telford
Shropshire
TF1 7FT

Customer Services and Sales Hotline

Call our Customer Services
Centre for all your national
sales enquiries.

0870 240 2400
sales@hager.co.uk

Customer Services and Sales Faxline

0870 240 0400

Technical Helpline

Technical Engineers offer both
national and local support.

0870 607 6677
technical@hager.co.uk

Technical Faxline

01952 675557

Hager Online

Visit our website for up to date
news on Hager and for general
brand information e-mail us.

www.hager.co.uk
info@hager.co.uk

TEHALIT

