



SL Skirting Systems

Cable Management Products

uPVC





Tehalit is part of the Hager group. And that's important to you. It means you'll enjoy the benefits of massive on-going investment in better manufacturing resources, research and development and customer service plus a cross-fertilisation of skills and technologies between the member companies. Hager itself was founded in 1955. It began as a family business and is still independently owned, even though, today, it is one of the world's leading manufacturers and suppliers of electrical control and distribution systems.

In addition to Tehalit cable management systems the group includes Hager, Klik and Ashley.



Customer service centre for national sales enquiries.

Technical engineers offer both national and local support.

Help is just a call or click away

Sales Hotline

For all your sales enquiries.
e-mail:

0870 240 2400
sales@hager.co.uk

Technical Helpline

For all your technical enquiries.
e-mail:

0870 607 6677
technical@hager.co.uk

Hager Online

www.hager.co.uk

For general information on Hager brands.
e-mail:

info@hager.co.uk

hager

ashley

klik

TEHALIT



Hager offer a comprehensive range of electrical distribution equipment up to 1600 Amps



Ashley, whose wiring accessories are synonymous with quality and reliability.



Klik has transformed the speed and efficiency of electrical connections.



Tehalit products provide the answers for every cable management situation.

SL Skirting Systems Cable Management Products


Installing cables in a skirting is an elegant, economical and efficient means of distributing power and data. Whatever the cable type SL provides a flexible system to cope with future demands with minimal disruption. Skirting systems can be installed efficiently in next to no time with no damage to the wall and no dirt.

The SL system has transformed this principle into reality with its technical sophistication and style. The SL skirting system offers two or three compartments to accommodate different cable types.

Socket plinths can be installed for power sockets, aerials, speakers, phone, etc. wherever needed.

Main features include:

- Base and lid supplied complete to simplify ordering.
- Pre-drilled base to reduce installation time.
- Low voltage and data cables can be accommodated.
- Ideal for new buildings or refurbishment.
- Available in various colours and finishes. Consult us for further information.
- Carpet lid option.



Products are available with a flexible lip system to ensure good fit with wall. This helps when the wall is not true providing a neat finish.

Corner accessories ensure smooth joints and clear-cut ends.

SL is a stylishly designed system. By virtue of its aesthetic design and wide range of colours, the SL system harmonises with modern interior decoration schemes.

Electrical service management for international five star jet setters

Manchester airport's latest £35 million five star hotel have used Tehalit's SL cable management system.

As a five star hotel where aesthetics is vital, the subtle, unobtrusive styling of Tehalit's SL trunking range was a major reason for its specification.

Cables could not be run up from the concrete flooring, so an unobtrusive, stylish cable management system was needed.

For installation, Tehalit SL trunking is cut to length and fixed in place. Power outlets or data sockets then sit on top of the trunking where they are needed, screwed to the back of the wall and wired in. Finally the trunking lid is cut to length and fitted. The cover for the outlet box sits over the trunking and its lid, so even if the lid is not cut absolutely flush, the outlet's cover masks it. It is equally as simple to add more sockets or change the position of socket outlets in the future.



Aesthetics was vital with the SL trunking having to fit in with a number of different styles in the hotel. Each bedroom for instance is themed in one of four styles: Scandinavian, Oriental, Italian or Maritime. Tehalit SL trunking is available in a number of colours and styles.



Tehalit fast fit trunking minimises tenant disruption

Minimal disruption through fast installation and simple future proofing for new electrical demands were the twin benefits realised by Edinburgh council tenants in the refurbishment of two fourteen storey block of flats using Tehalit's SL trunking.

As occupied flats, Scottish Power had to contact and organise convenient times with each tenant for the electrical refurbishment. Once in a flat, the team of contractor's needed to complete the electrical rewiring with minimum disruption, so speed of installation was vital.

The fast fit features of Tehalit's SL trunking meant that each of the two bedroom and one bedroom flats typically took just one day to rewire.

The ability to place and fix sockets on site was important because the position of fitted units varied from flat to flat.

Increasingly domestic users want more power, telephone and television sockets. Using Tehalit SL effectively future proofs the flats for increased electrical needs.

Adding more sockets anywhere along the trunking is relatively simple and avoids replastering and redecoration.

In a residential setting aesthetics is also important. Tehalit SL trunking is a slimline UPVC system with rounded edges for a soft unobtrusive feel. The council specified the SL trunking that complemented the shape of the existing wooden skirting.




Ordering Information


Trunking Part Numbers

[SL_20051](#) / [9010](#)


SL refers to the skirting trunking range.
20051 refers to the dimensions.
 First two digits represent depth i.e. 20 = 20mm
9010 refers to RAL No.




Internal Corner




External Corner




Flat Corner




Coupling piece




End Cap
Right




End Cap
Left




Skirting to architrave adaptor
Right




Skirting to architrave adaptor
Left



Carpet Skirting
End Cap
Right



Carpet Skirting
End Cap
Left



Socket Plinth

SL skirting trunking



- Standard length: 2m.
- Base (pre drilled).

Ordering information

- Base and lid supplied complete.
- When ordering please add the RAL reference number to the part number.
E.g. SL 20051/**7035** for light grey.

Standard colours


- 7035 light grey (RAL 7035).
- 9010 pure white (RAL 9010).

Please consult us for other colours and finishes.

description

*capacity for
2.5mm² cable*

*cat
ref.*



skirting - 50mm

size: 50mm x 20mm

27

SL 20051/____

internal corner with adaptor
for mini trunking 15 x 15mm

L 2611/____

internal corner

M 5551/____

external corner

M 5552/____

end cap right

M 5553/____

end cap left

M 5554/____

coupling piece

M 5555/____


skirting to architrave adaptor

right for SL 17052

L 2248/____

left for SL 17052

L 2249/____



skirting - 70mm

size: 70mm x 20mm

39

SL 20071/____

internal corner with adaptor for
mini trunking 15 x 15mm

L 2621/____

internal corner

M 5561/____

external corner

M 5562/____

end cap right

M 5563/____

end cap left

M 5564/____

coupling piece

M 5565/____

skirting to architrave adaptor

right for SL 17052

L 2258/____

left for SL 17052

L 2259/____

SL skirting trunking



- Standard length: 2m
- Base (pre drilled).

Ordering information

- Base and lid supplied complete.
- When ordering please add the RAL reference number to the part number.
E.g. SL 15100/**7035** for light grey.

Standard colours


- 7035 light grey (RAL 7035).
- 9010 pure white (RAL 9010).

Please consult us for other colours and finishes.

description

*capacity for
2.5mm² cable*

*cat
ref.*



skirting - 100mm

size: 100mm x 15mm

36

SL 15100/____

internal corner

M 5651/____

external corner

M 5652/____

end cap right


M 5653/____

end cap left

M 5654/____

coupling piece

M 5655/____



skirting - 100mm

size: 100mm x 25mm

57

SL 25100/____

internal corner

M 5681/____

external corner

M 5682/____

end cap right

M 5683/____

end cap left

M 5684/____

coupling piece

M 5685/____

SL skirting trunking



- Standard length: 2m.
- Base (pre drilled).

Ordering information





- Base and lid supplied complete.
- When ordering please add the RAL reference number to the part number.
E.g. SL 20053/**7035** for light grey.

Standard colours

- 7035 light grey (RAL 7035)
- 9010 pure white (RAL 9010)

Please consult us for other colours and finishes.

<i>description</i>	<i>capacity for 2.5mm² cable</i>	<i>cat ref.</i>
carpet skirting - 50mm		
size: 50mm x 20mm	27	SL 20053/....
end caps right		M 5333/....
end caps left		M 5334/....
carpet skirting - 70mm		
size: 70mm x 20mm	39	SL 20073/....
end caps right		M 5343/....
end caps left		M 5344
carpet skirting - 100mm		
size: 100mm x 15mm	36	SL 15103/....
end cap		R 9163/....
carpet skirting - 100mm		
size: 100mm x 25mm	57	SL 25103/....
end cap		R 9173/....
architrave skirting - for 50 and 70mm		
size: 52mm x 17mm	22	SL 17052/....
flat corner		L 2247/....
Designed to take the trunking around doors frames		



SL skirting trunking & floor surface trunking accessories

	<i>description</i>	<i>cat ref.</i>
 L2402	socket plinths for 50 and 70mm trunking 1 gang socket plinths dimensions 98 (w) x 56(d) x 177(h)mm	L 2272/....
	2 gang socket plinths dimensions 156 (w) x 56(d) x 177(h)mm	L 2321/....
	70mm adaptor for standard mounting boxes	L 2402/....
 L2350	socket plinths for 100mm trunking 1 gang socket plinths dimensions 99 (w) x 60(d) x 195(h)mm	L 2350/....
	2 gang socket plinths dimensions 159 (w) x 60(d) x 195(h)mm	L 2360/....
 L2360		

Floor surface trunking

	<i>description</i>	<i>cat ref.</i>
	floor trunking - size 41mm x 11mm one piece construction - light grey (RAL 7035)	SL 11040/7035
	floor trunking - size 75mm x 17mm base and lid supplied complete - light grey (RAL 7035)	SL 18075/7035


EK cornice trunking

EK is the perfect solution for taking cables from floor to ceiling, and around the ceiling, of residential or commercial premises. Ideally suited for refurbishment projects where available time on site is limited.



Advantages of the system

- A discrete design that blends in with the decor.
- A 2.5m profile which will link floor to ceiling.
- A full set of accessories for all configurations.
- Base punching to ease installation.
- Two compartments allow segregation of circuits.
- Large cable capacity.



The lid fixing is adjustable to allow for variations in the building. This is ideal for refurbishment projects.

EK cornice trunking











- Material rigid uPVC.
- Standard length: 2.5m.
- 2 compartment.

- Ordering information**
- Base and lid supplied complete.

standard colours
9010 pure white (RAL 9010).

Please consult us for other colours and finishes.

	<i>description</i>	<i>cat ref.</i>
	trunking - size 40mm x 40mm base and lid	EK 40040/....
EK 40040/....	internal and flat corner	L 2771/....
	external corner	L 2772/....
L 2771/....	end cap	L 2773/....
	coupling	L 2774/....
L 2772/....	adaptor for mini trunking 15mm x 15mm	L 2778/....
	connection to SL20051 (can also be ordered in 7035 - light grey (RAL 7035))	L 2768/....
L 2773/....	connection to SL20071 (can also be ordered in 7035 - light grey (RAL 7035))	L 2769/....
	T piece	L 2779/....
L 2774/....		
		
L 2778/....		
		
L 2768/....		
		
L 2779/....		

<i>product reference</i>	<i>qty</i>	<i>page n°</i>	<i>product reference</i>	<i>qty</i>	<i>page n°</i>	<i>product reference</i>	<i>qty</i>	<i>page n°</i>	<i>product reference</i>	<i>qty</i>	<i>page n°</i>
E			M			R					
EK 40040/____	50m	10	M 5333/____	1	7	R9163/____	1	7			
			M 5334/____	1	7	R9173/____	1	7			
L			M 5343/____	1	7				S		
L 2247/____	1	7	M 5344/____	1	7	SL 11040/7035	70m	8			
L 2248/____	1	5	M 5551/____	1	5	SL 15100/____	30m	6			
L 2249/____	1	5	M 5552/____	1	5	SL 15103/____	30m	7			
L 2258/____	1	5	M 5553/____	1	5	SL 17052/____	24m	7			
L 2259/____	1	5	M 5554/____	1	5	SL 18075/7035	32m	8			
L 2272/____	1	8	M 5555/____	1	5	SL 20051/____	48m	5			
L 2321/____	1	8	M 5561/____	1	5	SL 20053/____	48m	7			
L 2350/____	1	8	M 5562/____	1	5	SL 20071/____	36m	5			
L 2360/____	1	8	M 5563/____	1	5	SL 20073/____	36m	7			
L 2402/____	1	8	M 5564/____	1	5	SL 25100/____	18m	6			
L 2611/____	1	5	M 5565/____	1	5	SL 25103/____	18m	7			
L 2621/____	1	5	M 5651/____	1	6						
L 2768/____	1	10	M 5652/____	1	6						
L 2769/____	1	10	M 5653/____	1	6						
L 2771/____	1	10	M 5654/____	1	6						
L 2772/____	1	10	M 5655/____	1	6						
L 2773/____	1	10	M 5681/____	1	6						
L 2774/____	1	10	M 5682/____	1	6						
L 2778/____	1	10	M 5683/____	1	6						
L 2779/____	1	10	M 5684/____	1	6						
			M 5685/____	1	6						

The SL Skirting Trunking range form part of Tehalit's cable management offer.
Other product ranges include:

C60 / CA60
Perimeter Systems



LF/LFS
General Purpose Trunking




Pacpole and Pacpost
Powerpoles and Powerposts



We also have a range of Halogen Free systems suitable for use where self-extinguishing low flammability and minimal release of gases are essential. Typical areas include public buildings, schools, and hospitals.




BR/BRA/BRS
Commercial Dado Trunking
uPVC, aluminium and steel



LFG
High Strength GRP Trunking



Panel Trunking
Slotted Trunking



Specifying the system to suit your project, or ordering the necessary components really couldn't be easier. However, if you need any assistance please consult our sales or technical helpline.

Sales Hotline
e-mail:

0870 240 2400
sales@hager.co.uk

Technical Helpline
e-mail:

0870 607 6677
technical@hager.co.uk

Should you require a sales visit or require further information with reference to a **particular project** please complete your details and return to us, via the attached reply paid card.

Information regarding the products featured in this brochure can be found on our website:


www.hager.co.uk




Now available

A series of leaflets explaining the versatility of Tehalit's C60 / CA 60C60 / CA60 Perimeter Systems and BR/BRA/BRS Commercial Dado Trunking uPVC, aluminium and steel ranges.







Bristol Regional Centre

135 Aztec West
Almondsbury
Bristol
BS32 4UB
Tel: 01454 616245
Fax: 01454 617172

Falkirk Regional Centre

5a Callendar Business Park
Callendar Road
Falkirk
FK1 1XR
Tel: 01324 632128
Fax: 01324 631294

London Regional Centre

Warwick House
65-66 Queen Street
London
EC4R 1EB
Tel: 0207 3293891
Fax: 0207 3293893

Midlands Regional Centre

Hortonwood 50
Telford
Shropshire
TF1 7FT
Tel: 01952 675615
Fax: 01952 675626

Wakefield Regional Centre

Brindley Way
Wakefield 41 Ind. Estate
Wakefield
West Yorkshire
WF2 0XQ
Tel: 01924 871103
Fax: 01924 824429

Visit our website:

www.hager.co.uk

e-mail us @

info@hager.co.uk
sales@hager.co.uk
technical@hager.co.uk

Ireland

Hager Ltd.
Unit M2 Furry Park
Industrial Estate,
Santry,
Dublin 9.
Ireland.

From ROI

Tel: 1890 551 502
Fax: 1890 551 503

From NI

Tel: 028 90 773310
Fax: 028 90 773572

Email: info@hager.ie
Web: <http://www.hager.ie>



National Sales Hotline
0870 240 2400

National Technical Support Helpline
0870 607 6677

National Sales Faxline
0870 240 0400

Visit our website:
www.hager.co.uk

e-mail us @
info@hager.co.uk
sales@hager.co.uk
technical@hager.co.uk

Hager Ltd
Hortonwood 50
Telford
Shropshire
TF1 4BR

BUSINESS REPLY SERVICE
Licence No SY868

Your Contact Details

Name: _____

Position: _____

Company: _____

Nature of Business:

- Consultant Contractor
Wholesaler Local Authority
Housing Association

Other: _____

Address: _____

Post Code: _____

Tel: _____

Email: _____

Project Title: _____

Type of Project:

- New Build
Refurbishment:
Future Need:

I would like to see a sample of:

- SL skirting SL carpet
EK cornice

I would like to receive a copy of:-

- C60 perimeter systems catalogue
BR dado systems catalogue

I would like to receive updates on the latest
news & products from Hager.

Hager Ltd
Hortonwood 50
Telford
Shropshire
TF1 4BR

BUSINESS REPLY SERVICE
Licence No SY868

Your Contact Details

Name: _____

Position: _____

Company: _____

Nature of Business:

- Consultant Contractor
Wholesaler Local Authority
Housing Association

Other: _____

Address: _____

Post Code: _____

Tel: _____

Email: _____

Project Title: _____

Type of Project:

- New Build
Refurbishment:
Future Need:

I would like to see a sample of:

- SL skirting SL carpet
EK cornice

I would like to receive a copy of:-

- C60 perimeter systems catalogue
BR dado systems catalogue

I would like to receive updates on the latest
news & products from Hager.